

Mailguard® Confined Space X-ray Scanner

Ordering Specifications:

X-ray Generator Capability

Rated 90 kV constant potential peak, high reliability, high frequency X-ray generator. Not film-safe. If film-safety, color monitor or full digital functionality is required, visit autoclearus.com or call for AUTOCLEAR Desktop 3920 or conveyORIZED 4025.

Current: 1 mA maximum

Cooling: Sealed oil bath, air

Compartment Size

18" (45.7 cm) Wide

21" (53.3 cm) Deep

14" (35.6 cm) High

Viewing Method

Direct view

Fluoroscopic Inspection Screen Size

17" (43.2 cm) x 17" (43.2 cm)

The full screen area is imaged, but thick parcels may need to be viewed twice.

Penetration

11mm of steel equivalent

Resolution

#40-UL AWG Copper wire

Input Voltage and

Power Requirements

110-130 volt or 210-250 volt,
(Specify voltage when ordering)

Single phase AC,

50/60 Hertz, under 250 watts

Overall Size and Weight

30.5" (77.5 cm) High

22.5" (57.2 cm) Wide

23.5" (59.7 cm) Deep

350 lbs (159 kg)

400 lbs (182 kg) crated

Radiation Safety

Dual Safety interlocks

Panel operating switch

Double shielded glass

Lockable power switch



Meets or exceeds Federal

Standard 21 CFR 1020.40 and

all applicable International Radiation
and CE Marking Standards.

Custom Options

- Transport Cart
- Rental or lease
- Extended Warranty
- CE Marking



Distributor:



Security Pro USA
264 S. La Cienega Blvd. Suite 451
Beverly Hills, CA 90211
Phone (310) 475-7780 Fax (310) 475-7065